Structure Open Back Close Coupled Pan



| No. | Description                                | Product Code | Fixings Included? | Gross Weight | Net Weight |
|-----|--|--------------|-------------------|--------------|------------|
| 1   | Structure Cistern inc. Flush Fitting & Lid | C450S        | Yes               |              |            |
| 2   | Structure Toilet Seat                      | TS450S       | Yes               |              |            |
| 3   | Structure Open Back Close Coupled Pan      | P450S        | Yes               |              |            |





### **Cistern Settings**


Full Flush Volume: 4.5L Reduced Flush Volume: 3L



DIAGRAMS NOT TO SCALE ALL DIMENSIONS IN MM TOLERANCE OF ± 5MM







#### **FAQ**

What side is the inlet located? **Right hand side**Are there any other compatible seats? **No**Can this pan be used with a side connection outlet pipe? **Yes**The cistern lid won't shut/the cistern isn't working correctly. **Ensure the inlet and flush valves are set to the correct heights.** 

| TS450S Dimensions              |             |  |  |  |
|--------------------------------|-------------|--|--|--|
| Seat/Lid front to back         | 435mm/445mm |  |  |  |
| Seat/Lid left to right         | 330mm/345mm |  |  |  |
| Ring hole front to back        | 285mm       |  |  |  |
| Ring hole left to right 210mm  |             |  |  |  |
| Seat overall thickness         | 47mm        |  |  |  |
| Min/Max adjustment for fixings | 55mm-160mm  |  |  |  |

Structure Comfort Height Open Back Close Coupled Pan




| No. | Description  | Product Code | Fixings Included? | Gross Weight | Net Weight |
|-----|--|--------------|-------------------|--------------|------------|
| 1   | Structure Cistern inc. Flush Fitting & Lid           | C450S        | Yes               |              |            |
| 2   | Structure Toilet Seat                                | TS450S       | Yes               |              |            |
| 3   | Structure Comfort Height Open Back Close Coupled Pan | PC455S       | Yes               |              |            |





### **Cistern Settings**

Full Flush Volume: 4.5L Reduced Flush Volume: 3L









### **FAQ**

What side is the inlet located? **Right hand side**Are there any other compatible seats? **No**Can this pan be used with a side connection outlet pipe? **Yes**The cistern lid won't shut/the cistern isn't working correctly. **Ensure the inlet and flush valves are set to the correct heights.** 

| TS450S Dimensions              |             |  |  |  |  |
|--------------------------------|-------------|--|--|--|--|
| Seat/Lid front to back         | 435mm/445mm |  |  |  |  |
| Seat/Lid left to right         | 330mm/345mm |  |  |  |  |
| Ring hole front to back        | 285mm       |  |  |  |  |
| Ring hole left to right        | 210mm       |  |  |  |  |
| Seat overall thickness         | 47mm        |  |  |  |  |
| Min/Max adjustment for fixings | 55mm-160mm  |  |  |  |  |


Structure
Back to Wall Pan



| 1 | No. | Description                | Product Code | Fixings Included? | Gross Weight | Net Weight |
|---|-----|----------------------------|--------------|-------------------|--------------|------------|
|   | 1   | Structure Toilet Seat      | TS450S       | Yes               |              |            |
|   | 2   | Structure Back to Wall Pan | BTW450S      | Yes               |              |            |







### **FAQ**

Are there any other compatible seats? No

| TS450S Dimensions              |             |  |  |  |
|--------------------------------|-------------|--|--|--|
| Seat/Lid front to back         | 435mm/445mm |  |  |  |
| Seat/Lid left to right         | 330mm/345mm |  |  |  |
| Ring hole front to back        | 285mm       |  |  |  |
| Ring hole left to right        | 210mm       |  |  |  |
| Seat overall thickness         | 47mm        |  |  |  |
| Min/Max adjustment for fixings | 55mm-160mm  |  |  |  |


Structure
Comfort Back to Wall Pan





| No | Description                        | Product Code | Fixings Included? | Gross Weight | Net Weight |
|----|------------------------------------|--------------|-------------------|--------------|------------|
| 1  | Structure Toilet Seat              | TS450S       | Yes               |              |            |
| 2  | Structure Comfort Back to Wall Pan | BTWC450S     | Yes               |              |            |











DIAGRAMS NOT TO SCALE ALL DIMENSIONS IN MM TOLERANCE OF ± 5MM

### **FAQ**

Are there any other compatible seats?  $\ensuremath{\text{\textbf{No}}}$ 

| TS450S Dimensions                  |             |  |  |  |
|------------------------------------|-------------|--|--|--|
| Seat/Lid front to back 435mm/445mm |             |  |  |  |
| Seat/Lid left to right             | 330mm/345mm |  |  |  |
| Ring hole front to back            | 285mm       |  |  |  |
| Ring hole left to right            | 210mm       |  |  |  |
| Seat overall thickness             | 47mm        |  |  |  |
| Min/Max adjustment for fixings     | 55mm-160mm  |  |  |  |

Structure Comfort Height Fully Enclosed Pan



| No. | Description                                 | Product Code | Fixings Included? | Gross Weight | Net Weight |
|-----|---|--------------|-------------------|--------------|------------|
| 1   | Structure Cistern inc. Flush Fitting & Lid  | C450S        | Yes               |              |            |
| 2   | Structure Toilet Seat                       | TS450S       | Yes               |              |            |
| 3   | Structure Comfort Height Fully Enclosed Pan | PC450S       | Yes               |              |            |





### **Cistern Settings**


Full Flush Volume: 4.5L Reduced Flush Volume: 3L



DIAGRAMS NOT TO SCALE ALL DIMENSIONS IN MM TOLERANCE OF ± 5MM







#### **FAQ**

What side is the inlet located? **Right hand side**Are there any other compatible seats? **No**Can this pan be used with a side connection outlet pipe? **No**The cistern lid won't shut/the cistern isn't working correctly. **Ensure the inlet and flush valves are set to the correct heights.** 

| TS450S Dimensions              |             |  |  |  |
|--------------------------------|-------------|--|--|--|
| Seat/Lid front to back         | 435mm/445mm |  |  |  |
| Seat/Lid left to right         | 330mm/345mm |  |  |  |
| Ring hole front to back        | 285mm       |  |  |  |
| Ring hole left to right        | 210mm       |  |  |  |
| Seat overall thickness         | 47mm        |  |  |  |
| Min/Max adjustment for fixings | 55mm-160mm  |  |  |  |

Structure Fully Enclosed Close Coupled Pan



| No. | Description                                | Product Code | Fixings Included? | Gross Weight | Net Weight |
|-----|--|--------------|-------------------|--------------|------------|
| 1   | Structure Cistern inc. Flush Fitting & Lid | C450S        | Yes               |              |            |
| 2   | Structure Toilet Seat                      | TS450S       | Yes               |              |            |
| 3   | Structure Fully Enclosed Close Coupled Pan | PF450S       | Yes               |              |            |





### **Cistern Settings**


Full Flush Volume: 4.5L Reduced Flush Volume: 3L



DIAGRAMS NOT TO SCALE ALL DIMENSIONS IN MM TOLERANCE OF ± 5MM







#### **FAQ**

What side is the inlet located? **Right hand side**Are there any other compatible seats? **No**Can this pan be used with a side connection outlet pipe? **No** 

The cistern lid won't shut/the cistern isn't working correctly.

Ensure the inlet and flush valves are set to the correct heights.

| PF450S Pan Dimensions           |       |  |  |  |  |  |
|---------------------------------|-------|--|--|--|--|--|
| Front to Back                   | 515mm |  |  |  |  |  |
| Left to Right front             | 205mm |  |  |  |  |  |
| Left to Right back              | 225mm |  |  |  |  |  |
| Central width                   | 230mm |  |  |  |  |  |
| Height of inlet centre to floor | 400mm |  |  |  |  |  |

| TS450S Dimensions              |             |  |  |
|--------------------------------|-------------|--|--|
| Seat/Lid front to back         | 435mm/445mm |  |  |
| Seat/Lid left to right         | 330mm/345mm |  |  |
| Ring hole front to back        | 285mm       |  |  |
| Ring hole left to right        | 210mm       |  |  |
| Seat overall thickness         | 47mm        |  |  |
| Min/Max adjustment for fixings | 55mm-160mm  |  |  |


Structure Wall Hung Pan



| 1 | ٧o. | Description                | Product Code | Fixings Included? | Gross Weight | Net Weight |
|---|-----|----------------------------|--------------|-------------------|--------------|------------|
|   | 1   | Structure Slim Toilet Seat | TS451S       | Yes               |              |            |
|   | 2   | Structure Wall Hung Pan    | WH450S       | Yes               |              |            |



DIAGRAMS NOT TO SCALE ALL DIMENSIONS IN MM TOLERANCE OF ± 5MM



### **FAQ**

Are there any other compatible seats? Yes TS450S


Structure Slim Basin and Pedestal



| No. | Description          | Product Code | Fixings Included? | Gross Weight | Net Weight |
|-----|----------------------|--------------|-------------------|--------------|------------|
| 1   | Structure Slim Basin | SB450S       | No                |              |            |
| 2   | Structure Pedestal   | PE450S       | No                |              |            |



Water Depth (Bottom of bowl to the underside of overflow) - **70MM** 



#### **FAQ**

Can the basin be wall hung?

Yes, finish with a chrome bottle trap.

Are the wall fixings supplied?

No. Use fixings appropriate to the installation at hand.


| PE450S FAQ                                      | Answer |
|---|--------|
| Distance at rear base from wall when fitted MIN | 85mm   |
| Distance at rear base from wall when fitted MAX | 95mm   |
| Foot front to back depth                        | 140mm  |
| Outside width front                             | 130mm  |
| Outside width back                              | 170mm  |
| Cavity width (pipe fit)                         | 95mm   |
| Cavity depth (pipe fit)                         | 130mm  |


Structure 450mm Wall Hung Basin



| No. | Description           | Product Code | Fixings Included? | Gross Weight | Net Weight |
|-----|-----------------------|--------------|-------------------|--------------|------------|
| 1   | Structure 450mm Basin | SB455S       | No                |              |            |
| 2   | Structure Trap        | TRAP6        | Yes               |              |            |







### **FAQ**

What is the depth of the basin to the overflow?  $\ensuremath{\textbf{72mm}}$ 

 $\label{thm:linear} \mbox{Are wall fittings supplied? No, use Fischer or similar suitable fixings for installation.}$ 

Is there a pedestal available? No, but R2 Nashville Pedestal (NVPED) is compatible

Structure 600mm Wall Hung Basin





| No. | Description           | Product Code | Fixings Included? | Gross Weight | Net Weight |
|-----|-----------------------|--------------|-------------------|--------------|------------|
| 1   | Structure 600mm Basin | SB356S       | No                |              |            |
| 2   | Structure Trap        | TRAP6        | Yes               |              |            |






Note: Can be wall hung or mounted on the Agenda pedestal or semi-pedestal.







#### **FAQ**

What is the depth of the basin to the overflow?  $\bf 60mm$ 

Are wall fittings supplied? No, use Fischer or similar suitable fixings for installation.

PE350S Dimensions: 165mm (w) x 700mm (h) x 170mm (d) SMP350S Dimensions: 180mm (w) x 270mm (h) x 310mm (d)

Structure 700mm Wall Hung Basin





| N | lo. | Description           | Product Code | Fixings Included? | Gross Weight | Net Weight |
|---|-----|-----------------------|--------------|-------------------|--------------|------------|
|   | 1   | Structure 700mm Basin | SB357S       | No                |              |            |
| 2 | 2   | Structure Trap        | TRAP6        | Yes               |              |            |






Note: Can be wall hung or mounted on the Agenda pedestal or semi-pedestal.







#### **FAQ**

What is the depth of the basin to the overflow?  ${\bf 70mm}$ 

Are wall fittings supplied? No, use Fischer or similar suitable fixings for installation.

PE350S Dimensions: 165mm (w) x 700mm (h) x 170mm (d) SMP350S Dimensions: 180mm (w) x 270mm (h) x 310mm (d)

Structure 800mm Wall Hung Basin





| N | lo. | Description           | Product Code | Fixings Included? | Gross Weight | Net Weight |
|---|-----|-----------------------|--------------|-------------------|--------------|------------|
|   | 1   | Structure 800mm Basin | SB358S       | No                |              |            |
|   | 2   | Structure Trap        | TRAP6        | Yes               |              |            |






Note: Can be wall hung or mounted on the Agenda pedestal or semi-pedestal.







#### **FAQ**

What is the depth of the basin to the overflow?  ${\bf 70mm}$ 

Are wall fittings supplied? No, use Fischer or similar suitable fixings for installation.


PE350S Dimensions: 165mm (w) x 700mm (h) x 170mm (d) SMP350S Dimensions: 180mm (w) x 270mm (h) x 310mm (d)

Structure Semi Pedestal + Pedestal



| No. | Description                | Product Code | Fixings Included? | Gross Weight | Net Weight |
|-----|----------------------------|--------------|-------------------|--------------|------------|
| 1   | Structure Ceramic Pedestal | PE350S       | N/A               |              |            |
| 2   | Structure Semi Pedestal    | SMP350S      | Yes               |              |            |





### **NOTES**


Those pedestals are only for use on SB356S/SB357S/SB358S basins. For SB450S, use pedestal PE450S.


Structure 550 Semi-Countertop Standard Basin



| No. | Description                                    | Product Code | Fixings Included? | Gross Weight | Net Weight |
|-----|--|--------------|-------------------|--------------|------------|
| 1   | Structure 550mm Semi-Countertop Standard Basin | SCSB453S     | Yes               |              |            |







### **FAQ**


Is there a cutting template supplied? **Yes.**What is the water depth of the basin? **96mm (to the overflow)** 


Structure 540 Semi-Countertop Slim Basin



| I | No. | Description                                | Product Code | Fixings Included? | Gross Weight | Net Weight |
|---|-----|--|--------------|-------------------|--------------|------------|
|   | 1   | Structure 540mm Semi-Countertop Slim Basin | SCSB452S     | Yes               |              |            |







DIAGRAMS NOT TO SCALE

### **FAQ**

Is there a cutting template supplied? **Yes.**What is the water depth of the basin? **82mm (to the overflow)**